



SPECIFICATIONS

		4-Door R-WB735P5MS	3-Door R-WB560P9MS
Model		R-WB735P5MS	R-WB560P9MS
Image			
Net Capacity (L)	Total	590	465
	Freezer	160	122
	Refrigerator	430	343
Refrigerator Compartment	Selectable Mode Compartment	•	-
	Fresh Select Compartment	-	•
	Tempered Glass Shelves	3	3
	LED Light	•	•
Vegetable Compartment	Aero-Care Vege Compartment	•	-
	Open-Assist Handle	•	-
	Bright Vegetable Compartment with LED	-	•
Freezer Compartment	Easy Twist Ice Maker (on door)	•	-
	Movable Twist Ice Tray	-	•
	Quick Freezing	•	•
	Slide Type Double-deck Drawer	-	•
	Swing Pocket	•	-
	Extra Wide Case	•	-
General Features	Inverter Control	•	•
	Electronic Control	•	•
	VIP (Vacuum Insulation Panel)	•	•
	Dual Sensing Control (with Eco Thermo-Sensor)	•	•
	Dual Fan Cooling	•	•
	Door Alarm	•	•
Common Features	Refrigerant	R-600a	R-600a
	CFC-Free	•	•
	HFC-Free	•	•
	Nano Titanium	•	-
	Triple Power Filter	-	•
Power Supply (V,Hz)		220-240, 50/60	220-240, 50/60
Plug		BS 3PIN	BS 3PIN
Dimension (mm)	Width	860	750
	Height	1,835	1,795
	Depth with Handle	808	797
	Depth without Handle	777	760
Color		Glass Black (GBK)	Glass Black (GBK)

Interior




Net 590L




Net 465L

- Refrigerator Compartment
- Vegetable Compartment
- Freezer Compartment

Dimensions (mm)



Net 590L



Net 465L

□:Space required for ventilation.

Hitachi Home Electronics Asia (S) Pte. Ltd. Tel: +65 6536 2520 Fax: +65 6536 2521
Email: enquiries.hhes.vq@hitachi.com Website: www.homeappliances.hitachi.com/sg

Printed Date: 19th February 2020.
Net Capacity measured according to ISO (International Organization for Standardization) Standard (ISO Storage Volume).
All models & specifications in content are subjected to change without prior notice. Color tone of actual products may differ from those shown in this catalogue.

HITACHI

Refrigerator

French Bottom Freezer

HITACHI
Inspire the Next



Enjoy the taste of fresh



Glass Black (GBK)

Glass Black (GBK)

French Bottom Freezer (590L)



Vacuum Insulation Panel
 Outer Bag
 Inner Bag
 Glass Wool
High Level of Heat Insulation
 Glass Fiber about 4µm

INVERTER × Dual Fan Cooling

Provides optimum cooling in both the freezer and refrigerator compartments, something a single fan can't do. Improved Dual Fan Cooling with dedicated fans for each compartment ensures energy saving and powerful cooling. This is supported by the Eco Thermo-Sensor in each compartment that detects any temperature change separately to enable the ideal temperature change to be maintained in each of the compartments at all times.

Energy Saving

Controlling how much and to which compartment chilled air is delivered, it assures no wasted energy thus helping it acquire energy saving ratings.



Stabilizer Free

Even without a special stabilizer, Hitachi's inverter refrigerator can operate under wide voltage fluctuations. Tested by Hitachi.

Cools under wide voltage fluctuations
130v-300v

Powerful Cooling

Even if the ambient temperature reaches as high as 60°C, every corner inside the refrigerator is still thoroughly cooled. Tested by Hitachi.

Cools even at
60°C

Long Cool Keeper

The temperature in the freezer compartment is maintained to keep food fresh in the event of a power cut. Tested by Hitachi. Hours may differ depending on models.

Cooling Retention
15 Hours
 Even during power cut

Easy-View Refrigerator Compartment

The often-used refrigerator compartment is positioned for easy use and offers a wide field of vision. Even with a lot of food stored, a glance is all you need to see everything, so it's easy to put in and take out items.

Super Big REF Compartment

Super big capacity allows you to store plenty of food, so there's no worry if you bulk buy or purchase too much.



Extra Wide Interior

The wide 71cm interior lets you store large dishes and big items.



Easy to Access

User-friendly height enables easy viewing and quick access to everything stored in the vegetable compartment.



Outstanding Convenience

Touch Screen Controller

Flat glass panel controls let you change settings with a simple touch. And the surface has been tempered, so a wipe is all it takes to clean it.



ECO

ECO lamp

Automatically lights when refrigerator operation is stable.

Dual Fan

Dual Fan lamp

Automatically lights during Dual Fan operation.

Selectable Mode Compartment

The select lever provides an easy way to switch between the Vegetable and Dairy/Meat modes.



Vegetable Mode



Dairy/Meat Mode



Double Layer Door Pockets

The new Double Layer Door Pockets are designed to enable well-organized storage of different sized bottles, seasonings and spices.



Bright, Energy-Saving LED Lights



Easy Twist Ice Maker

Located in the door of the freezer compartment. As well as leaving more space for storing items, this new style makes it easy to make and take out ice.

Easy to twist the ice

The conveniently located lever lets you easily twist the ice with a single finger.



Easy water supply
 It's easy to supply clean, bottled water.



Spacious Layout

Double Sliding Cases for well-organized storage



Extra wide case for big items



Advanced Japanese Technology.

Aero-care Vege Compartment


A platinum catalyst maintains a high concentration of carbon dioxide in the compartment. This large vegetable compartment keeps items fresher for longer.

Optimum storage conditions keep vegetables fresh!

Vegetables continue to respire after being harvested but lowering the surrounding temperature and increasing the concentration of carbon dioxide slows down this respiration. These conditions help prevent vegetables from losing their freshness.


Platinum Catalyst
Generates CO₂

The platinum catalyst breaks down ethylene gas and odor components to generate even more carbon dioxide.



Airtight Structure
Holds CO₂

The airtight structure maintains a higher concentration of carbon dioxide than in the air. As a result, the vegetables release less of their nutrients and water and so retain their freshness.




Humidity Controller
Maintains perfect humidity without condensation

Excess moisture inside the vegetable compartment collects at the aluminum panel and the condensation is absorbed by the transpiration board.

Aero-care Vege Compartment Maintains the Freshness of Vegetables
As a result of joint research by Hokkaido University and Hitachi, a platinum catalyst is now used for the first time in a home refrigerator. Even at low temperatures, the catalyst increases the amount of carbon dioxide in the Aero-care Vege Compartment. Professor Atsushi Fukuoka, Catalysis Research Center, Hokkaido University


Open-Assist Handle

The open-assist handle enables opening with little effort even when a lot of items are stored and the compartment is heavy.



Keeps vegetables fresh for seven days!

Comparison after 7 days of Aero-Care and non Aero-Care storage



R-WB735P5MS Net 590L



Glass Black (GBK)

Refrigerator Compartment

- Aero-care Vege Compartment
- Open Assist Handle
- Double Layer Door Pockets
- LED Light
- Tempered Glass Shelves

Freezer Compartment

- Easy Twist Ice Maker
- Double Slide Case
- Extra Wide Case

General Features


- VIP (Vacuum Insulation Panel)
- Inverter Control
- Dual Fan Cooling
- Dual Sensing Control (with Eco Thermo-Sensor)
- Touch Screen Controller
- ECO Lamp • Dual Fan Lamp
- Nano Titanium Filter • Moldproof Door Gasket
- No Frost • CFC-Free • HFC-Free

French Bottom Freezer (465L)




Easy to See and Use French Door, Bottom Drawer Freezer

See and reach for your favorite food with less bending and lifting. You can now take food out from the fridge compartment easily.



French doors take up less room space when opened, making it ideal for small spaces. More cold air is kept inside making it energy saving.



INVERTER × Dual Fan Cooling

Provides optimum cooling in both the freezer and refrigerator compartments, something a single fan can't do. Improved Dual Fan Cooling with dedicated fans for each compartment ensures energy saving and powerful cooling. This is supported by the Eco Thermo-Sensor in each compartment that detects any temperature change separately to enable the ideal temperature change to be maintained in each of the compartments at all times.

Energy Saving

Controlling how much and to which compartment chilled air is delivered, it assures no wasted energy thus helping it acquire energy saving ratings.



Stabilizer Free

Even without a special stabilizer, Hitachi's inverter refrigerator can operate under wide voltage fluctuations. Tested by Hitachi.

Cools under wide voltage fluctuations
130v-300v

Powerful Cooling

Even if the ambient temperature reaches as high as 60°C, every corner inside the refrigerator is still thoroughly cooled. Tested by Hitachi.

Cools even at
60°C


Long Cool Keeper

The temperature in the freezer compartment is maintained to keep food fresh in the event of a power cut. Tested by Hitachi. Hours may differ depending on models.

Cooling Retention
12 Hours
Even during power cut

Fresh Select

The Select Lever lets you adjust the inside temperature by switching between the two modes.



Bright Vegetable Compartment with LED Light

With automatic lighted-LED, vegetable compartment becomes brighter and easier to find fresh food.



Double-Deck Vegetable Storage

Select the vegetable mode of the Fresh Select to enjoy more storage space for vegetables.



Powerful Cooling

When you want to cool quickly and powerfully, switch the quick cooling mode ON.

Approx. **28%***
Faster Cooling

* Tested by Hitachi. Comparison between conventional in normal mode and new 3 Door French Bottom Freezer in Quick Cooling mode on top shelf.



Touch Screen Controller

A simple touch allows you to change the settings.



Movable Twist Ice Tray

For efficient use of storage space, ice tray can be moved or even removed as you like.



Powerful Deodorization

Equipped with a Triple Power Filter that catches and removes 7 odour components.



Methyl Mercaptan
Odours of Onions and garlic

Ammonia
Odours of Raw fish

Acetaldehyde
Odours of Vinegar

Jumbo Door Pocket

For a storage of up to 8 bottles of 2.0L.



Easy-To-Open Door Design

Unique handle design for easy opening of fridge doors.



R-WB560P9MS Net 465L



Glass Black (GBK)

Refrigerator Compartment

- Fresh Select
- Bright Vegetable Compartment with LED Light
- LED Lighting
- Tempered Glass Shelves
- Quick Cooling
- Jumbo Door Pocket

Freezer Compartment

- Double-Deck Drawer
- Movable Twist Ice Tray
- Quick Freezing

General Features

- Inverter Control
- Dual Fan Cooling
- Dual Sensing Control (with Eco Thermo-Sensor)
- Touch Screen Controller
- Powerful Deodorization
- Moldproof Door Gasket
- No Frost
- CFC-Free
- HFC-Free